

Product data sheet

Characteristics

AZ5DE025

Cable end, Lineryg TR cable ends, twin conductor, grey, 2.5mm², for insulated cable, medium size, 5 sets of 50



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.32 USD



Main

Range of Product	Lineryg
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	Dispenser pack
Quantity per Set	5 sets of 50
Cable cross section	0.004 ln ² (2.5 mm ²)

Complementary

Cable end type	Twin conductor
Additional information	Without marker tag holder
Color	Gray
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	2
AWG Gauge	AWG 14
Bezel size	Ø 4.2 x 7.8 mm
Tube diameter	0.1 ln (3.2 mm)
Length	0.7 ln (18.5 mm)
Tube length	0.4 ln (10 mm)
Net Weight	0.320 Lb(US) (0.145 kg)

Environment

Product Certifications	cCSAus
Ambient Air Temperature for Operation	-4.000000000...221.000000000 °F (-20...105 °C)

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110515893
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.787 In (2.000 cm)
Package 1 Weight	0.018 Oz (0.500 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	250
Package 2 Height	5.118 In (13.000 cm)
Package 2 Width	2.756 In (7.000 cm)
Package 2 Length	4.961 In (12.600 cm)
Package 2 Weight	4.444 Oz (126.000 g)
Unit Type of Package 3	S04
Number of Units in Package 3	10000
Package 3 Height	11.811 In (30.000 cm)
Package 3 Width	15.748 In (40.000 cm)
Package 3 Length	23.622 In (60.000 cm)
Package 3 Weight	14.092 Lb(US) (6.392 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**