

Product data sheet

Characteristics

BCH2MB0133CF5C

servo motor BCH, Lexium 28, 40mm, 100W, 0.076kg.cm², with oil seal, with key, brake, leads connection



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 862.16 USD



Main

Range Compatibility	Lexium 28
Product or Component Type	Servo motor
Device short name	BCH2

Complementary

Maximum mechanical speed	5000 Rpm
[Us] rated supply voltage	220 V 110 V
Phase	Three phase Single phase
Continuous stall current	0.81 A
Continuous stall torque	2.83 Lbf.In (0.32 N.m) LXM26D 0.9 A, 220 V, single phase 2.83 Lbf.In (0.32 N.m) LXM26D 0.9 A, 220 V, three phase 2.83 Lbf.In (0.32 N.m) LXM28... 0.9 A, 220 V, single phase 2.83 Lbf.In (0.32 N.m) LXM28... 0.9 A, 220 V, three phase 2.83 Lbf.In (0.32 N.m) LXM28... 1.8 A, 110 V, single phase
Continuous power	100 W
Peak stall torque	8.50 Lbf.In (0.96 N.m) LXM26D 0.9 A, 220 V, single phase 8.50 Lbf.In (0.96 N.m) LXM26D 0.9 A, 220 V, three phase 8.50 Lbf.In (0.96 N.m) LXM28... 0.9 A, 220 V, single phase 8.50 Lbf.In (0.96 N.m) LXM28... 0.9 A, 220 V, three phase 8.50 Lbf.In (0.96 N.m) LXM28... 1.8 A, 110 V, single phase
Nominal output power	100 W LXM26D 0.9 A, 220 V, single phase 100 W LXM26D 0.9 A, 220 V, three phase 100 W LXM28... 0.9 A, 220 V, single phase 100 W LXM28... 0.9 A, 220 V, three phase 100 W LXM28... 1.8 A, 110 V, single phase
Nominal torque	2.83 Lbf.In (0.32 N.m) LXM26D 0.9 A, 220 V, single phase 2.83 Lbf.In (0.32 N.m) LXM26D 0.9 A, 220 V, three phase 2.83 Lbf.In (0.32 N.m) LXM28... 0.9 A, 220 V, single phase 2.83 Lbf.In (0.32 N.m) LXM28... 0.9 A, 220 V, three phase 2.83 Lbf.In (0.32 N.m) LXM28... 1.8 A, 110 V, single phase

Nominal speed	3000 rpm LXM26D 0.9 A, 220 V, single phase 3000 rpm LXM26D 0.9 A, 220 V, three phase 3000 rpm LXM28... 0.9 A, 220 V, single phase 3000 rpm LXM28... 0.9 A, 220 V, three phase 3000 rpm LXM28... 1.8 A, 110 V, single phase
Maximum current Irms	2.65 A LXM28... 0.1 kW, 220 V 2.65 A LXM28... 0.1 kW, 110 V
Maximum permanent current	0.89 A
Product compatibility	LXM26D servo drive 0.1 kW, 220 V, single phase LXM26D servo drive 0.1 kW, 220 V, three phase LXM28... servo drive 0.1 kW, 220 V, single phase LXM28... servo drive 0.1 kW, 220 V, three phase LXM28... servo drive 0.1 kW, 110 V, single phase
Shaft end	Keyed
Shaft diameter	0.31 In (8 mm)
Shaft length	0.98 In (25 mm)
Key width	0.12 In (3 mm)
Feedback type	20 bits single turn absolute encoder
Holding brake	With
Holding torque	2.83 Lbf.In (0.32 N.m) built-in
Mounting Support	Asian standard flange
Motor flange size	1.57 In (40 mm)
Electrical connection	Free lead
Torque constant	0.4 N.M/A 68 °F (20 °C)
Back emf constant	24 V/Krpm 68 °F (20 °C)
Rotor inertia	0.076 Kg.Cm ²
Stator resistance	23.4 Ohm 68 °F (20 °C)
Stator inductance	20.6 MH 68 °F (20 °C)
Stator electrical time constant	0.88 Ms 68 °F (20 °C)
Maximum radial force Fr	85 N 3000 rpm
Maximum axial force Fa	40 N
Brake pull-in power	4.35 W
Type of cooling	Natural convection
Length	5.12 In (130 mm)
Number of motor stacks	2
Centring collar diameter	1.18 In (30 mm)
Centring collar depth	0.12 In (3 mm)
Number of mounting holes	4
Mounting holes diameter	0.18 In (4.5 mm)
Circle diameter of the mounting holes	1.81 In (46 mm)
Distance shaft shoulder-flange	0.12 In (3 mm)
Net Weight	1.70 Lb(US) (0.77 kg)

Environment

IP Degree of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)

Ordering and shipping details

Category	US1000I22000
Discount Schedule	000I
GTIN	3606480733475
Returnability	No
Country of origin	US

Packing Units


Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.15 In (8.0 cm)
Package 1 Width	5.12 In (13.0 cm)
Package 1 Length	9.45 In (24.0 cm)
Package 1 Weight	2.31 Lb(US) (1.05 kg)
Unit Type of Package 2	S02
Number of Units in Package 2	3
Package 2 Height	5.91 In (15.0 cm)
Package 2 Width	11.81 In (30.0 cm)
Package 2 Length	15.75 In (40.0 cm)
Package 2 Weight	6.96 Lb(US) (3.156 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage


Servo Motor without shaft sealing ring and LXM28AU01●●● Servo Drive



- 1 : Peak torque
- 2 : Continuous torque

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

Servo Motor with shaft sealing ring and LXM28AU01●●● Servo Drive



- 1 : Peak torque
- 2 : Continuous torque

Product Life Status : Commercialised