



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BDA140401



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
 Approvals: UL Listed - CSA Certified - IEC Rated
 Mounting Type: I-Line
 Terminal Type: ON end: I-Line / OFF end: Mechanical Lugs
 Weight: 1
 Depth:
 Height:
 Width:
 Mounting Height: 1.5

Specification:

Description: PowerPact B-Frame Thermal Magnetic Circuit Breaker
 Number of Poles: 1-Pole
 Ampere Rating: 040
 Voltage Rating: 480Y/277 VAC
 Interrupting Rating: 25kA at240VAC 18kA at480Y/277VAC
 Circuit Breaker Rating: 80% Rated
 Fixed AC Magnetic Trip: Hold: 400A - Trip: 600A