



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BDA24015Y6



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application:	Provides overload and short circuit protection
Approvals:	UL Listed - CSA Certified - IEC Rated
Mounting Type:	I-Line
Terminal Type:	ON end: I-Line / OFF end: Mechanical Lugs
Weight:	2
Depth:	
Height:	
Width:	
Mounting Height:	3

Specification:

Description:	PowerPact B-Frame Thermal Magnetic Circuit Breaker
Number of Poles:	2-Pole
Ampere Rating:	015
Voltage Rating:	480Y/277 VAC
Interrupting Rating:	25kA at240VAC 18kA at480Y/277VAC
Circuit Breaker Rating:	80% Rated
Fixed AC Magnetic Trip:	Hold: 320A - Trip: 480A