



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**BGA140151**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

General Application: Provides overload and short circuit protection  
 Approvals: UL Listed - CSA Certified - IEC Rated  
 Mounting Type: I-Line  
 Terminal Type: ON end: I-Line / OFF end: Mechanical Lugs  
 Weight: 1  
 Depth:  
 Height:  
 Width:  
 Mounting Height: 1.5

**Specification:**

Description: PowerPact B-Frame Thermal Magnetic Circuit Breaker  
 Number of Poles: 1-Pole  
 Ampere Rating: 015  
 Voltage Rating: 480Y/277 VAC  
 Interrupting Rating: 65kA at240VAC 35kA at480Y/277VAC  
 Circuit Breaker Rating: 80% Rated  
 Fixed AC Magnetic Trip: Hold: 320A - Trip: 480A