



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BGA260606



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
Approvals: UL Listed - CSA Certified - IEC Rated
Mounting Type: I-Line
Terminal Type: ON end: I-Line / OFF end: Mechanical Lugs
Weight: 2
Depth:
Height:
Width:
Mounting Height: 3

Specification:

Description: PowerPact B-Frame Thermal Magnetic Circuit Breaker
Number of Poles: 2-Pole
Ampere Rating: 060
Voltage Rating: 600Y VAC
Interrupting Rating: 65kA at240VAC 35kA at480VAC 18kA at600Y/347VAC
Circuit Breaker Rating: 80% Rated
Fixed AC Magnetic Trip: Hold: 640A - Trip: 960A