


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
BGA261104

 **SQUARE D**
 by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

| | |
|----------------------|--|
| General Application: | Provides overload and short circuit protection |
| Approvals: | UL Listed - CSA Certified - IEC Rated |
| Mounting Type: | I-Line |
| Terminal Type: | ON end: I-Line / OFF end: Mechanical Lugs |
| Weight: | 2 |
| Depth: | |
| Height: | |
| Width: | |
| Mounting Height: | 3 |

Specification:

| | |
|-------------------------|--|
| Description: | PowerPact B-Frame Thermal Magnetic Circuit Breaker |
| Number of Poles: | 2-Pole |
| Ampere Rating: | 110 |
| Voltage Rating: | 600Y VAC |
| Interrupting Rating: | 65kA at240VAC 35kA at480VAC 18kA at600Y/347VAC |
| Circuit Breaker Rating: | 80% Rated |
| Fixed AC Magnetic Trip: | Hold: 1000A - Trip: 1500A |