


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
BGA261253

 **SQUARE D**
 by **Schneider Electric**
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 General Application: Provides overload and short circuit protection
 Approvals: UL Listed - CSA Certified - IEC Rated
 Mounting Type: I-Line
 Terminal Type: ON end: I-Line / OFF end: Mechanical Lugs
 Weight: 2
 Depth:
 Height:
 Width:
 Mounting Height: 3

Specification:
 Description: PowerPact B-Frame Thermal Magnetic Circuit Breaker
 Number of Poles: 2-Pole
 Ampere Rating: 125
 Voltage Rating: 600Y VAC
 Interrupting Rating: 65kA at240VAC 35kA at480VAC 18kA at600Y/347VAC
 Circuit Breaker Rating: 80% Rated
 Fixed AC Magnetic Trip: Hold: 1000A - Trip: 1500A