



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**BGA36030**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

General Application:	Provides overload and short circuit protection
Approvals:	UL Listed - CSA Certified - IEC Rated
Mounting Type:	I-Line
Terminal Type:	ON end: I-Line / OFF end: Mechanical Lugs
Weight:	3
Depth:	
Height:	
Width:	
Mounting Height:	4.5

**Specification:**

Description:	PowerPact B-Frame Thermal Magnetic Circuit Breaker
Number of Poles:	3-Pole
Ampere Rating:	030
Voltage Rating:	600Y VAC
Interrupting Rating:	65kA at240VAC 35kA at480VAC 18kA at600Y/347VAC
Circuit Breaker Rating:	80% Rated
Fixed AC Magnetic Trip:	Hold: 400A - Trip: 600A