



Part No.:

BMH0702P31F1A



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Technical Information:

Frame Size (mm):	70
Degree of Protection (Shaft / housing):	IP65 / I P65
Maximum Current (Arms):	9.68
Holding brake:	Yes
Encoder Type:	ABS Single turn 128 Sin/Cos period
Torque Constant (Nm/A):	0.84
CSA:	Yes
RoHS:	Yes
Weight without brake (kg / lb):	5.07 / 2.3

Description:

Family:	BMH
Maximum Permissible Speed (rpm):	8000
Continuous Stall Torque (Nm / lbs-in):	2.48 / 21.9
Peak Torque (Nm / lbs-in):	7.44 / 65.85

Specification: