



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BMH0702T37F1A



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Frame Size (mm): 70
 Degree of Protection (Shaft / housing): IP65 / I P65
 Maximum Current (Arms): 17.71
 Holding brake: Yes
 Encoder Type: ABS Multi turn 16 Sin/Cos period
 Torque Constant (Nm/A): 0.46
 CSA: Yes
 RoHS: Yes
 Weight without brake (kg / lb): 5.07 / 2.3

Description:

Family: BMH
 Maximum Permissible Speed (rpm): 8000
 Continuous Stall Torque (Nm / lbs-in): 2.48 / 21.9
 Peak Torque (Nm / lbs-in): 7.44 / 65.85

Specification: