


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BMH0703P16A2A



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Frame Size (mm): 70
 Degree of Protection (Shaft / housing): IP54 / IP65
 Maximum Current (Arms): 12.57
 Holding brake: No
 Encoder Type: ABS Single turn 16 Sin/Cos period
 Torque Constant (Nm/A): 0.87
 CSA: Yes
 RoHS: Yes
 Weight without brake (kg / lb): 6.61 / 3

Specification:

Description:
 Family: BMH
 Maximum Permissible Speed (rpm): 8000
 Continuous Stall Torque (Nm / lbs-in): 3.40 / 30.1
 Peak Torque (Nm / lbs-in): 10.2 / 90.28