


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BMH1401P02A2A



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Frame Size (mm):	140
Degree of Protection (Shaft / housing):	IP54 / IP65
Maximum Current (Arms):	29.8
Holding brake:	No
Encoder Type:	ABS Multi turn 128 Sin/Cos period
Torque Constant (Nm/A)	1.2
CSA:	Yes
RoHS:	Yes
Weight without brake (kg / lb):	17.64 / 8.0

Specification:

Description:	BMH
Family:	4000
Maximum Permissible Speed (rpm):	10.3 / 91.2
Continuous Stall Torque (Nm / lbs-in):	39.9 / 353.1
Peak Torque (Nm / lbs-in):	