


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BMH1903P22F2A



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Frame Size (mm):	190
Degree of Protection (Shaft / housing):	IP65 / I P65
Maximum Current (Arms):	124.5
Holding brake:	Yes
Encoder Type:	ABS Multi turn 128 Sin/Cos period
Torque Constant (Nm/A):	1.8
CSA:	Yes
RoHS:	Yes
Weight without brake (kg / lb):	94.80 / 43

Description:

Family:	BMH
Maximum Permissible Speed (rpm):	3500
Continuous Stall Torque (Nm / lbs-in):	65 / 575.3
Peak Torque (Nm / lbs-in):	195 / 1725.9

Specification: