


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BMH2053P21A2A



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Frame Size (mm):	205
Degree of Protection (Shaft / housing):	IP65 / I P65
Maximum Current (Arms):	107.4
Holding brake:	No
Encoder Type:	ABS Single turn 128 Sin/Cos period
Torque Constant (Nm/A):	3.5
CSA:	Yes
RoHS:	Yes
Weight without brake (kg / lb):	147.70 / 67

Description:	
Family:	BMH
Maximum Permissible Speed (rpm):	3800
Continuous Stall Torque (Nm / lbs-in):	88 / 778.9
Peak Torque (Nm / lbs-in):	330 / 2920.7

Specification: