



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**BMXAMI0410H**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Mounting: Any slot except 0  
 Isolation Between Channels: 1400 VDC  
 Isolation Between Channels and Bus: 300 VDC  
 UL & CSA: Yes  
 CE: Yes  
 RoHS: Yes  
 Class 1 Div 2 CSA: Yes  
 GOST/BV/GL/RMRS/ABS: Yes  
 Weight [kg]: 0.143

**Specification:**

Description:  
 Selection: M340 PAC  
 Conf.Coating - 25C to 70C op.temp.: Yes  
 Input Voltage Range: ± 10 V, ± 5 V, 0 to 10 V, 0 to 5 V, 1 to 5 V  
 Input Current: 0 to 20 mA, 4 to 20 mA, ± 20 mA  
 Output Voltage Range:  
 Output Current:  
 Connection Type: BMXFCA500/BMXFTW301S/BMXFTW501S/ABE7CPA410/BMXFCA150/BMXFCA300  
 Number of Inputs: 4  
 Number of Outputs: