



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**BMXP3420102**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:	
Mounting:	slot 00/rack 0
UL & CSA:	Yes
CE:	Yes
RoHS:	Yes
Class 1 Div 2 CSA:	Yes
GOST/BV/GL/RMRS/ABS:	Yes
Weight [kg]:	0.55

Specification:	
Description:	M340 PAC
Selection:	
Number of Racks:	Supports 4 with 4, 6, 8 or 12 slots, max. number of slots: 48
Number of I/O:	1,024 discrete channels & 256 analog channels
Integrated Communication Ports:	1 USB port, 1 ModBus/Serial port & 1 CANopen2 master
Memory:	4,096 KB RAM & 8 MB SD Flash