



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Uninterruptible power supply (UPS)
Battery type	Lead-acid battery
Topology	Line interactive
Quantity per set	Set of 1
Reset	Automatic reset
Range of product	Easy UPS 1Ph BVS Series

Complementary

Type of installation	Indoor
Energy values	156 J
Type of signal	Stepped approximation to a sinewave
Protection device type	Surge protection device (SPD) Miniature circuit breaker (MCB) Fuse
Input voltage	230 V AC
Output voltage	230 V AC
IP degree of protection	IP20
Transfer time	6 ms typical : 10 ms maximum
Network frequency	45...65 Hz
Power range	650 VA 375 W
Electrical connection	Input: 1 inlet IEC 320 C14 Output: 6 outlet IEC 320 C13
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Number of batteries	1
Charging time	8 H
Battery voltage	12 V
Battery life	5 Year(S)
Net weight	4.5 Kg
Height	92.5 Mm
Width	160.5 Mm
Depth	305 Mm

Environment

Relative humidity	0...90 %, non-condensing
Operating altitude	0...6561 ft
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product certifications	CE

Physical

Mounting support	Wall Floor
------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.000 Cm
Package 1 Width	23.000 Cm
Package 1 Length	37.000 Cm
Package 1 Weight	4.983 Kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30.000 Cm
Package 2 Width	40.000 Cm
Package 2 Length	60.000 Cm
Package 2 Weight	20.960 Kg
Unit Type of Package 3	P12
Number of Units in Package 3	32
Package 3 Height	90.000 Cm
Package 3 Width	80.000 Cm
Package 3 Length	120.000 Cm
Package 3 Weight	179.680 Kg
SCC14	10731304338465

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years
----------	---------

Product Life Status : **Commercialised**