



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Product or component type	Uninterruptible power supply (UPS)
Battery type	Lead-acid battery
Topology	Line interactive
Quantity per set	Set of 1
Reset	Automatic reset
Range of product	Easy UPS 1Ph BVS Series

## Complementary

Type of installation	Indoor
Energy values	156 J
Type of signal	Stepped approximation to a sinewave
Protection device type	Surge protection device (SPD) Miniature circuit breaker (MCB) Fuse
Input voltage	230 V AC
Output voltage	230 V AC
IP degree of protection	IP20
Transfer time	6 ms typical : 10 ms maximum
Network frequency	45...65 Hz
Power range	800 VA 450 W
Electrical connection	Input: 1 inlet IEC 320 C14 Output: 6 outlet IEC 320 C13
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Number of batteries	1
Charging time	8 H
Battery voltage	12 V
Battery life	5 Year(S)
Net weight	5.3 Kg
Height	92.5 Mm
Width	160.5 Mm
Depth	305 Mm

## Environment

Relative humidity	0...90 %, non-condensing
Operating altitude	0...6561 ft
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product certifications	CE

## Physical

Mounting support	Wall Floor
------------------	---------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.200 Cm
Package 1 Width	16.500 Cm
Package 1 Length	30.500 Cm
Package 1 Weight	5.298 Kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30.000 Cm
Package 2 Width	40.000 Cm
Package 2 Length	60.000 Cm
Package 2 Weight	21.842 Kg
Unit Type of Package 3	P12
Number of Units in Package 3	32
Package 3 Height	90.000 Cm
Package 3 Width	80.000 Cm
Package 3 Length	120.000 Cm
Package 3 Weight	186.736 Kg
SCC14	10731304338502

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	2 years
----------	---------

Product Life Status : **Commercialised**