

# Product data sheet


## Characteristics

# DF14AM1

Auxiliary contact block, TeSys DF, 1NC, 5A, disconnecter, signalling contact, instantaneous

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 13.50 USD



### Main

Range	TeSys
Device short name	DF14
Product or Component Type	Auxiliary contact block
Auxiliary contacts operation	Instantaneous
Pole contact composition	1 NC
Connections - terminals	Faston connector

### Complementary

Range compatibility	TeSys TeSys DF
[Ui] rated insulation voltage	250 VAC
[Ue] rated operational voltage	24...240 V AC AC-15 24...240 V DC DC-13
[Ith] conventional free air thermal current	5 A
Minimum switching current	30 mA
Minimum switching voltage	10 V
Net Weight	0.06 Lb(US) (0.025 kg)

### Environment

Ambient Air Temperature for Operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)

### Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
GTIN	3389119407540
Returnability	No
Country of origin	TN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 In (2.0 cm)
Package 1 Width	1.18 In (3.0 cm)
Package 1 Length	3.15 In (8.0 cm)
Package 1 Weight	0.60 Oz (17.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	120
Package 2 Height	11.81 In (30.0 cm)
Package 2 Width	11.81 In (30.0 cm)
Package 2 Length	15.75 In (40.0 cm)
Package 2 Weight	5.34 Lb(US) (2.423 kg)

## Offer Sustainability

California proposition 65	WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**