

Product data sheet


Characteristics

DF14AM2

Auxiliary contact block, TeSys DF, 2NC, 5A, disconnecter, signalling contact, instantaneous

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 31.50 USD



Main

Range	TeSys
Device short name	DF14
Product or Component Type	Auxiliary contact block
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NC
Connections - terminals	Faston connector

Complementary

Range compatibility	TeSys TeSys DF
[Ui] rated insulation voltage	250 VAC
[Ue] rated operational voltage	24...240 V AC AC-15 24...240 V DC DC-13
[Ith] conventional free air thermal current	5 A
Minimum switching current	30 MA
Minimum switching voltage	10 V
Net Weight	0.06 Lb(US) (0.029 kg)

Environment

Ambient Air Temperature for Operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
GTIN	3389119407557
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 In (2.0 cm)
Package 1 Width	1.18 In (3.0 cm)
Package 1 Length	3.11 In (7.9 cm)
Package 1 Weight	0.60 Oz (17.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	120
Package 2 Height	11.81 In (30.0 cm)
Package 2 Width	11.81 In (30.0 cm)
Package 2 Length	15.75 In (40.0 cm)
Package 2 Weight	6.07 Lb(US) (2.753 kg)

Offer Sustainability

California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**