

# Product data sheet

## Characteristics

# DF2BN2000

NFC cartridge fuses, TeSys GS, cylindrical  
8.5mm x 31.5mm, fuse type gG, 400VAC, 20A,  
without striker, set of 10 parts

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 11.40 USD



### Main

Range of Product	TeSys fuse-disconnector
Product or Component Type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	400 V AC
Line Rated Current	20 A 400 V
Fuse size	8.5 x 31.5 mm
Fuse type	NFC
Quantity per Set	Set of 10

### Complementary

Fuse curve	GG
Net Weight	0.02 Lb(US) (0.01 kg)

### Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110499469
Returnability	No
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.47 In (1.2 cm)
Package 1 Width	1.34 In (3.4 cm)
Package 1 Length	3.54 In (9.0 cm)
Package 1 Weight	0.14 Oz (4.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	0.47 In (1.2 cm)
Package 2 Width	1.34 In (3.4 cm)
Package 2 Length	3.54 In (9.0 cm)
Package 2 Weight	1.55 Oz (44.0 g)
Unit Type of Package 3	S01
Number of Units in Package 3	1000
Package 3 Height	5.91 In (15.0 cm)
Package 3 Width	5.91 In (15.0 cm)
Package 3 Length	15.75 In (40.0 cm)
Package 3 Weight	9.78 Lb(US) (4.436 kg)

### Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**