

Product data sheet

Characteristics

DF2CA02

NFC cartridge fuses, TeSys GS, cylindrical 10mm x 38mm, fuse type aM, 500VAC, 2A, without striker, set of 10 parts

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 7.60 USD



Main

| | |
|--------------------------------|-------------------------|
| Range of Product | TeSys fuse-disconnector |
| Product or Component Type | Cartridge fuse |
| Device short name | DF2 |
| [Ue] rated operational voltage | 500 V AC |
| Fuse size | 10 x 38 mm |
| Fuse type | NFC |
| Quantity per Set | Set of 10 |

Complementary

| | |
|--------------------|-----------------------|
| Line Rated Current | 2 A 500 V |
| Fuse curve | AM |
| Net Weight | 0.02 Lb(US) (0.01 kg) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US1000I22621 |
| Discount Schedule | 000I |
| GTIN | 3389110501940 |
| Returnability | No |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|-------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.55 In (1.4 cm) |
| Package 1 Width | 1.57 In (4.0 cm) |
| Package 1 Length | 4.21 In (10.7 cm) |
| Package 1 Weight | 0.25 Oz (7.0 g) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |

| | |
|------------------------------|-------------------------|
| Package 2 Height | 1.57 In (4.0 cm) |
| Package 2 Width | 4.21 In (10.7 cm) |
| Package 2 Length | 0.55 In (1.4 cm) |
| Package 2 Weight | 2.72 Oz (77.0 g) |
| Unit Type of Package 3 | S01 |
| Number of Units in Package 3 | 720 |
| Package 3 Height | 5.91 In (15.0 cm) |
| Package 3 Width | 5.91 In (15.0 cm) |
| Package 3 Length | 15.75 In (40.0 cm) |
| Package 3 Weight | 12.70 Lb(US) (5.759 kg) |

Offer Sustainability

| | |
|----------------------------|--|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**