

# Product data sheet

## Characteristics

# DF2CA04

NFC cartridge fuses, TeSys GS, cylindrical 10mm x 38mm, fuse type aM, 500VAC, 4A, without striker, set of 10 parts

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 7.60 USD



### Main

Range of Product	TeSys fuse-disconnector
Product or Component Type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	500 V AC
Fuse size	10 x 38 mm
Fuse type	NFC
Quantity per Set	Set of 10

### Complementary

Line Rated Current	4 A 500 V
Fuse curve	AM
Net Weight	0.02 Lb(US) (0.01 kg)

### Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110501964
Returnability	No
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.51 In (1.3 cm)
Package 1 Width	4.25 In (10.8 cm)
Package 1 Length	1.57 In (4 cm)
Package 1 Weight	0.25 Oz (7 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	0.51 In (1.3 cm)
Package 2 Width	4.25 In (10.8 cm)
Package 2 Length	1.57 In (4 cm)
Package 2 Weight	2.75 Oz (78 g)
Unit Type of Package 3	S01
Number of Units in Package 3	720
Package 3 Height	5.91 In (15 cm)
Package 3 Width	5.91 In (15 cm)
Package 3 Length	15.75 In (40 cm)
Package 3 Weight	12.79 Lb(US) (5.8 kg)

### Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**