

Product data sheet

Characteristics

DF2EA08

NFC cartridge fuses, TeSys GS, cylindrical 14mm x 51mm, fuse type aM, 500VAC, 8A, without striker, set of 10 parts



Product availability: Non-Stock - Not normally stocked in distribution facility



Commercial status

This Product is Obsolete : JUL 12, 2021

⚠ This Product is Obsolete

Main

Range of Product	TeSys fuse-disconnector
Product or Component Type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	500 V AC
Fuse size	14 x 51 mm
Fuse type	NFC
Quantity per Set	Set of 10

Complementary

Line Rated Current	8 A 500 V
Fuse curve	AM
Net Weight	0.04 Lb(US) (0.02 kg)

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110502305
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 In (1.5 cm)
Package 1 Width	4.17 In (10.6 cm)
Package 1 Length	4.53 In (11.5 cm)
Package 1 Weight	0.63 Oz (18 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**