

Product data sheet

Characteristics

DF2FA50

NFC cartridge fuses, TeSys GS, cylindrical, 22mm x 58mm, fuse type aM, 690VAC, 50A, without striker, set of 10 parts

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 27.90 USD



Main

Range of Product	TeSys fuse-disconnector
Product or Component Type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	690 V AC
Fuse size	22 x 58 mm
Fuse type	NFC
Quantity per Set	Set of 10

Complementary

Line Rated Current	50 A 690 V
Fuse curve	AM
Net Weight	0.10 Lb(US) (0.045 kg)

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110502800
Returnability	No
Country of origin	TN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.98 In (2.5 cm)
Package 1 Width	4.45 In (11.3 cm)
Package 1 Length	4.72 In (12.0 cm)
Package 1 Weight	1.73 Oz (49.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	0.98 In (2.5 cm)
Package 2 Width	4.45 In (11.3 cm)
Package 2 Length	4.72 In (12.0 cm)
Package 2 Weight	18.45 Oz (523.0 g)
Unit Type of Package 3	S01
Number of Units in Package 3	120
Package 3 Height	5.91 In (15.0 cm)
Package 3 Width	5.91 In (15.0 cm)
Package 3 Length	15.75 In (40.0 cm)
Package 3 Weight	14.24 Lb(US) (6.46 kg)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**