

Product data sheet

Characteristics

DFCC1

Fuse carrier, TeSys DF, 1P, 30A, 600VAC, fuse class CC



Product availability: Stock - Normally stocked in distribution facility

Price*: 18.00 USD



Main

Range	TeSys
Product name	TeSys DF
Product or Component Type	Fuse carrier
Device short name	DFCC
Poles description	1P
Fuse type	, CC
Control type	Toggle padlockable
Utilisation category	AC-20B IEC 60947-3
[Ue] rated operational voltage	600 V AC
[Ie] rated operational current	30 A
[Ui] rated insulation voltage	600 V AC
[Uimp] rated impulse withstand voltage	6 KV
Short-circuit withstand	200 KA 600 V UL 512
Power dissipation in W	3 W maximum power dissipation by fuse

Complementary

Standards	UL 4248-1 UL 4248-4 CSA C22.2 No 4248-1 CSA C22.2 No 4248-4
Product certifications	UL Recognized[RETURN]CSA
Mounting Support	35 mm symmetrical DIN rail
Mounting position	Vertical +/- 23°
Connections - terminals	Screw clamp terminals 1 0.00...0.02 in ² (1...16 mm ²)rigid Screw clamp terminals 2 0.00...0.01 in ² (1...6 mm ²)rigid Screw clamp terminals 1 0.00...0.02 in ² (1...16 mm ²)flexible with or without screw clamp terminals 2 0.00...0.01 in ² (1...6 mm ²)flexible with or without
Tightening torque	17.70 Lbf.In (2 N.m) PZ2 17.70 Lbf.In (2 N.m) flat Ø 5.5 mm
Height	3.13 In (79.5 mm)
Width	0.69 In (17.5 mm)

Depth	2.40 In (61 mm)
Net Weight	0.09 Lb(US) (0.042 kg)
Quantity per Set	Set of 12

Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-40...158 °F (-40...70 °C) with derating above 20°C
Operating altitude	0...6561.68 ft (0...2000 m) without derating
IP degree of protection	IP20
Pollution degree	3
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility code	DFCC





Ordering and shipping details

Category	US10CP121714
Discount Schedule	OCP1
GTIN	3389119407267
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.67 In (1.7 cm)
Package 1 Width	2.44 In (6.2 cm)
Package 1 Length	3.15 In (8 cm)
Package 1 Weight	1.55 Oz (44 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	2.64 In (6.7 cm)
Package 2 Width	3.35 In (8.5 cm)
Package 2 Length	8.74 In (22.2 cm)
Package 2 Weight	19.82 Oz (562 g)
Unit Type of Package 3	S03
Number of Units in Package 3	192
Package 3 Height	11.81 In (30 cm)
Package 3 Width	11.81 In (30 cm)
Package 3 Length	15.75 In (40 cm)
Package 3 Weight	21.06 Lb(US) (9.554 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------