

# Product data sheet

## Characteristics

# DZ5CA007

Cable end, Lineryg TR cable ends, Single conductor, blue, 0.75mm<sup>2</sup>, medium size, markable, 10 sets of 100

Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.32 USD



### Main

|                           |   |
|---------------------------|---|
| Range of Product          | Lineryg                                       |
| Product or Component Type | Cable end                                     |
| Cable end size            | Medium  |
| Standards                 | NF C 63-023                                   |
| Type of Packing           | String of bags                                |
| Quantity per Set          | 10 sets of 100                                |
| Cable cross section       | 0.001 ln <sup>2</sup> (0.75 mm <sup>2</sup> ) |

### Complementary

|                        |                                   |
|------------------------|-----------------------------------|
| Cable end type         | Single conductor                  |
| Additional information | With integrated marker tag holder |
| Color                  | Blue                              |
| Bezel material         | Halogen-free plastic              |
| Tube material          | Copper ISO 1337                   |
| Number of cables       | 1                                 |
| AWG Gauge              | 20 AWG                            |
| Bezel size             | Ø 3.3 mm                          |
| Tube diameter          | 0.06 ln (1.5 mm)                  |
| Length                 | 0.6 ln (14 mm)                    |
| Tube length            | 0.3 ln (8 mm)                     |
| CAD overall depth      | 1.3 ln (32 mm)                    |
| Product Weight         | 0.35 Lb(US) (0.16 kg)             |

### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Product Certifications                | UL                         |
| Ambient Air Temperature for Operation | -4...221 °F (-20...105 °C) |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US1000I22621  |
| Discount Schedule | 000I          |
| GTIN              | 3389110535501 |
| Returnability     | Yes           |
| Country of origin | DE            |

## Packing Units

|                              |                           |
|------------------------------|---------------------------|
| Unit Type of Package 1       | PCE                       |
| Nbr. of units in pkg.        | 1                         |
| Package 1 Height             | 0.157 In (0.400 cm)       |
| Package 1 Width              | 0.157 In (0.400 cm)       |
| Package 1 Length             | 0.551 In (1.400 cm)       |
| Package weight(Lbs)          | 0.004 Oz (0.100 g)        |
| Unit Type of Package 2       | BB1                       |
| Number of Units in Package 2 | 1000                      |
| Package 2 Height             | 1.575 In (4.000 cm)       |
| Package 2 Width              | 4.331 In (11.000 cm)      |
| Package 2 Length             | 8.465 In (21.500 cm)      |
| Package 2 Weight             | 5.432 Oz (154.000 g)      |
| Unit Type of Package 3       | S04                       |
| Number of Units in Package 3 | 75000                     |
| Package 3 Height             | 11.811 In (30.000 cm)     |
| Package 3 Width              | 15.748 In (40.000 cm)     |
| Package 3 Length             | 23.622 In (60.000 cm)     |
| Package 3 Weight             | 27.073 Lb(US) (12.280 kg) |

## Environmental data

|  |   |
|--|---|
| REACH free of SVHC                     | Yes   |
| Toxic heavy metal free                 | Yes   |
| Mercury free                           | Yes   |
| Sustainable packaging                  | No  |
| Environmental Disclosure               | <a href="#">Product Environmental Profile</a>   |
| Packaging made with recycled cardboard | Yes   |
| Packaging without single use plastic   | No, we have minimized the use of plastic in the packaging in compliance with regulations and consider |
| REACH Regulation                       | Free of Substances of Very High Concern above the threshold <a href="#">↗</a>                         |
| EU RoHS Directive                      | Compliant <a href="#">↗</a>   |
| Halogen content performance            | Halogen free plastic parts product  |
| PVC free                               | Yes   |
| Silicon free                           | Yes   |
| Circularity Profile                    | <a href="#">End Of Life Information</a>   |
| Take-back                              | No  |
| WEEE Label                             | The product must be disposed on European Union markets following specific waste collection and new    |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|

Product Life Status : **Commercialised**