

# Product data sheet

## Characteristics

# DZ5CA025

Cable end, Linery TR cable ends, Single conductor, grey, 2.5mm<sup>2</sup>, medium size, markable, 10 sets of 100



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 0.32 USD



### Main

Range of Product	Linery
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.004 ln <sup>2</sup> (2.5 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	With integrated marker tag holder
Color	Gray
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 14
Bezel size	Ø 4.7 mm
Tube diameter	0.10 ln (2.5 mm)
Length	0.6 ln (14 mm)
Tube length	0.3 ln (8 mm)
CAD overall depth	1.3 ln (32 mm)
Net Weight	0.55 Lb(US) (0.25 kg)

### Environment

Product Certifications	UL
Ambient Air Temperature for Operation	-4.000000000...221.000000000 °F (-20...105 °C)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110535532
Returnability	No
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	1.339 In (3.400 cm)
Package 1 Weight	0.007 Oz (0.200 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	2.362 In (6.000 cm)
Package 2 Width	3.150 In (8.000 cm)
Package 2 Length	9.843 In (25.000 cm)
Package 2 Weight	7.443 Oz (211.000 g)
Unit Type of Package 3	S04
Number of Units in Package 3	50000
Package 3 Height	11.811 In (30.000 cm)
Package 3 Width	15.748 In (40.000 cm)
Package 3 Length	23.622 In (60.000 cm)
Package 3 Weight	25.739 Lb(US) (11.675 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**