

# Product data sheet

## Characteristics

# DZ5CA102D

Cable end, Linery TR cable ends, single conductor, red, 10mm<sup>2</sup>, for insulated cable, medium size, 10 sets of 100



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1.08 USD



### Main

Range of Product	Linery
Product or Component Type	Cable end
Cable end size	Medium
Standards	DIN 46228-4
Type of Packing	Bag
Quantity per Set	Set of 100
Cable cross section	0.02 In <sup>2</sup> (10 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	For additional marker tag holder
Color	Red
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 8
Bezel size	Ø 8.4 mm
Tube diameter	0.2 In (4.9 mm)
Length	0.9 In (22 mm)
Tube length	0.5 In (12 mm)
CAD overall depth	0.9 In (22 mm)
Net Weight	0.13 Lb(US) (0.06 kg)

### Environment

Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110211184
Returnability	No
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package 1 Weight	0.018 Oz (0.500 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	0.787 In (2.000 cm)
Package 2 Width	5.906 In (15.000 cm)
Package 2 Length	2.165 In (5.500 cm)
Package 2 Weight	1.905 Oz (54.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	3000
Package 3 Height	5.906 In (15.000 cm)
Package 3 Width	5.906 In (15.000 cm)
Package 3 Length	15.748 In (40.000 cm)
Package 3 Weight	3.984 Lb(US) (1.807 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**