

Product data sheet

Characteristics

DZ5CA102

Cable end, Linery TR cable ends, single conductor, brown, 10mm², medium size, 10 sets of 100



Product availability: Stock - Normally stocked in distribution facility

Price*: 0.72 USD



Main

| | |
|---------------------------|--|
| Range of Product | Linery |
| Product or Component Type | Cable end |
| Cable end size | Medium |
| Standards | NF C 63-023 |
| Type of Packing | Bag |
| Quantity per Set | Set of 100 |
| Cable cross section | 0.02 In ² (10 mm ²) |

Complementary

| | |
|------------------------|----------------------------------|
| Cable end type | Single conductor |
| Additional information | For additional marker tag holder |
| Color | Brown |
| Bezel material | Halogen-free plastic |
| Tube material | Copper ISO 1337 |
| Number of cables | 1 |
| AWG Gauge | AWG 8 |
| Bezel size | Ø 8.4 mm |
| Tube diameter | 0.2 In (4.9 mm) |
| Length | 0.9 In (22 mm) |
| Tube length | 0.5 In (12 mm) |
| CAD overall depth | 0.9 In (22 mm) |
| Net Weight | 0.126 Lb(US) (0.057 kg) |

Environment

| | |
|---------------------------------------|--|
| Ambient Air Temperature for Operation | -4.000000000...221.000000000 °F (-20...105 °C) |
|---------------------------------------|--|

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US1000I22621 |
| Discount Schedule | 000I |
| GTIN | 3389110535594 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.157 In (0.400 cm) |
| Package 1 Width | 0.157 In (0.400 cm) |
| Package 1 Length | 0.551 In (1.400 cm) |
| Package 1 Weight | 0.018 Oz (0.500 g) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 100 |
| Package 2 Height | 2.362 In (6.000 cm) |
| Package 2 Width | 0.787 In (2.000 cm) |
| Package 2 Length | 5.906 In (15.000 cm) |
| Package 2 Weight | 1.905 Oz (54.000 g) |
| Unit Type of Package 3 | S02 |
| Number of Units in Package 3 | 6000 |
| Package 3 Height | 5.906 In (15.000 cm) |
| Package 3 Width | 11.811 In (30.000 cm) |
| Package 3 Length | 15.748 In (40.000 cm) |
| Package 3 Weight | 7.798 Lb(US) (3.537 kg) |

Offer Sustainability

| | |
|-----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| PVC free | Yes |
| Halogen content performance | Halogen free plastic parts product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**