

# Product data sheet

## Characteristics

# DZ5CA253

Cable end, Linery TR cable ends, single conductor, black, 25mm<sup>2</sup>, medium size, 10 sets of 100



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1.10 USD



### Main

Range of Product	Linery
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	Bag
Quantity per Set	Set of 100
Cable cross section	0.04 In <sup>2</sup> (25 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	For additional marker tag holder
Color	Black
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 4
Bezel size	Ø 12 mm
Tube diameter	0.3 In (7.7 mm)
Length	1.4 In (36 mm)
Tube length	0.9 In (22 mm)
CAD overall depth	1.4 In (36 mm)
Net Weight	0.344 Lb(US) (0.156 kg)

### Environment

Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110535716
Returnability	No
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.472 In (1.200 cm)
Package 1 Width	0.551 In (1.400 cm)
Package 1 Length	1.260 In (3.200 cm)
Package 1 Weight	0.046 Oz (1.300 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	1.969 In (5.000 cm)
Package 2 Width	3.740 In (9.500 cm)
Package 2 Length	5.906 In (15.000 cm)
Package 2 Weight	4.656 Oz (132.000 g)
Unit Type of Package 3	S04
Number of Units in Package 3	7000
Package 3 Height	11.811 In (30.000 cm)
Package 3 Width	15.748 In (40.000 cm)
Package 3 Length	23.622 In (60.000 cm)
Package 3 Weight	23.184 Lb(US) (10.516 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**