

Product data sheet

Characteristics

DZ5CE005L12

Cable ends, Lineryg TR cable ends, single conductor, white, 0.5mm², for insulated cable, 10 sets of 100

Product availability: Non-Stock - Not normally stocked in distribution facility



Commercial status

This Product is Obsolete : SEP 18, 2023

 This Product is Obsolete

Main

Range of Product	Lineryg
Product or Component Type	Cable end
Cable end size	Long
Standards	NF C 63-023
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.0008 In ² (0.5 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	White
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	22 AWG
Bezel size	Ø 3 mm
Tube diameter	0.06 In (1.4 mm)
Length	0.7 In (16.8 mm)
Tube length	0.5 In (12 mm)
Product Weight	0.209 Lb(US) (0.095 kg)

Environment

Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------


Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110537147
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.08 In (0.2 cm)
Package 1 Width	0.08 In (0.2 cm)
Package 1 Length	0.6 In (1.5 cm)
Package weight(Lbs)	0.04 Oz (1 g)

Environmental data

REACH free of SVHC	Yes
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	No
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant 
Halogen content performance	Halogen free plastic parts product
PVC free	Yes
Silicon free	Yes
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and new

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **End of commerc. - Block**