

Product data sheet

Characteristics

DZ5CE007D

Cable ends, Linergy TR cable ends, single conductor, grey, 0.75mm², for insulated cable, 10 sets of 100



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.18 USD



Main

Range of Product	Linergy
Product or Component Type	Cable end
Cable end size	Medium
Standards	DIN 46228-4
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.00 In ² (0.75 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Gray
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 20
Bezel size	Ø 3.3 mm
Tube diameter	0.06 In (1.5 mm)
Length	0.55 In (14 mm)
Tube length	0.31 In (8 mm)
Net Weight	0.22 Lb(US) (0.1 kg)

Environment

Product Certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)




Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110211313
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.16 In (0.400 cm)
Package 1 Width	0.16 In (0.400 cm)
Package 1 Length	0.55 In (1.400 cm)
Package 1 Weight	0.00 Oz (0.100 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	0.98 In (2.500 cm)
Package 2 Width	4.33 In (11.000 cm)
Package 2 Length	7.09 In (18.000 cm)
Package 2 Weight	3.49 Oz (99.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	20000
Package 3 Height	5.91 In (15.000 cm)
Package 3 Width	5.91 In (15.000 cm)
Package 3 Length	15.75 In (40.000 cm)
Package 3 Weight	4.82 Lb(US) (2.186 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**