

# Product data sheet

## Characteristics

# DZ5CE015L6

Cable ends, Linergy TR cable ends, single conductor, black, 1.5mm<sup>2</sup>, for insulated cable, short size, 10 sets of 100



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 0.33 USD



### Main

Range of Product	Linergy
Product or Component Type	Cable end
Cable end size	Short
Standards	NF C 63-023
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.00 ln <sup>2</sup> (1.5 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Black
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 16
Bezel size	Ø 4 mm
Tube diameter	0.08 ln (2 mm)
Length	0.47 ln (12 mm)
Tube length	0.24 ln (6 mm)
Net Weight	0.24 Lb(US) (0.11 kg)

### Environment

Product Certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110536881
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.16 In (0.400 cm)
Package 1 Width	0.16 In (0.400 cm)
Package 1 Length	0.55 In (1.400 cm)
Package 1 Weight	0.00 Oz (0.100 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	0.98 In (2.500 cm)
Package 2 Width	4.33 In (11.000 cm)
Package 2 Length	7.09 In (18.000 cm)
Package 2 Weight	4.02 Oz (114.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	15000
Package 3 Height	5.91 In (15.000 cm)
Package 3 Width	5.91 In (15.000 cm)
Package 3 Length	15.75 In (40.000 cm)
Package 3 Weight	4.22 Lb(US) (1.913 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**