

# Product data sheet

## Characteristics

# DZ5CE020

Cable ends, Lineryy TR cable ends, single conductor, yellow, 2mm<sup>2</sup>, medium size, 10 sets of 100



Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.24 USD



### Main

Range of Product	Lineryy
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.003 ln <sup>2</sup> (2 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Yellow
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 14
Bezel size	Ø 4.2 mm
Tube diameter	0.09 ln (2.2 mm)
Length	0.6 ln (14 mm)
Tube length	0.3 ln (8 mm)
Net Weight	0.298 Lb(US) (0.135 kg)

### Environment

Ambient Air Temperature for Operation	-4.000000000...221.000000000 °F (-20...105 °C)
---------------------------------------	--

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110537109
Returnability	Yes
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package 1 Weight	0.004 Oz (0.100 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	0.984 In (2.500 cm)
Package 2 Width	4.331 In (11.000 cm)
Package 2 Length	7.087 In (18.000 cm)
Package 2 Weight	5.326 Oz (151.000 g)
Unit Type of Package 3	S02
Number of Units in Package 3	20000
Package 3 Height	5.906 In (15.000 cm)
Package 3 Width	11.811 In (30.000 cm)
Package 3 Length	15.748 In (40.000 cm)
Package 3 Weight	7.394 Lb(US) (3.354 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**