

Product data sheet

Characteristics

DZ5CE040

Cable ends, Linery TR cable ends, single conductor, 0.5mm², for un-insulated cable, medium size, 10 sets of 100



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.60 USD



Main

Range of Product	Linery
Product or Component Type	Cable end
Cable end size	Medium
Standards	DIN 46228-1
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.006 In ² (4 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Non-insulated
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 12
Bezel size	Ø 5.4 mm
Tube diameter	0.1 In (3.2 mm)
Length	0.5 In (12 mm)
Tube length	0.5 In (12 mm)
Net Weight	0.7 Lb(US) (0.3 kg)

Environment

Ambient Air Temperature for Operation	-4.000000000...221.000000000 °F (-20...105 °C)
---------------------------------------	--

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110537031
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package 1 Weight	0.007 Oz (0.200 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	0.591 In (1.500 cm)
Package 2 Width	1.575 In (4.000 cm)
Package 2 Length	2.362 In (6.000 cm)
Package 2 Weight	0.882 Oz (25.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	10000
Package 3 Height	5.906 In (15.000 cm)
Package 3 Width	5.906 In (15.000 cm)
Package 3 Length	15.748 In (40.000 cm)
Package 3 Weight	5.787 Lb(US) (2.625 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**