

# Product data sheet

## Characteristics

# DZ5CE062D

Cable ends, Linergy TR cable ends, single conductor, yellow, 6mm<sup>2</sup>, for insulated cable, medium size, 10 sets of 100



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 0.72 USD



### Main

Range of Product	Linergy
Product or Component Type	Cable end
Cable end size	Medium
Standards	DIN 46228-4
Type of Packing	Individual bag
Quantity per Set	Set of 100
Cable cross section	0.009 ln <sup>2</sup> (6 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Yellow
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 10
Bezel size	Ø 6.9 mm
Tube diameter	0.2 ln (3.9 mm)
Length	0.8 ln (20 mm)
Tube length	0.5 ln (12 mm)
Net Weight	0.099 Lb(US) (0.045 kg)

### Environment

Product Certifications	UL
Ambient Air Temperature for Operation	-4.000000000...221.000000000 °F (-20...105 °C)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110211436
Returnability	No
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.276 In (0.700 cm)
Package 1 Width	0.276 In (0.700 cm)
Package 1 Length	0.787 In (2.000 cm)
Package 1 Weight	0.011 Oz (0.300 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	0.787 In (2.000 cm)
Package 2 Width	4.134 In (10.500 cm)
Package 2 Length	4.724 In (12.000 cm)
Package 2 Weight	1.376 Oz (39.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	4000
Package 3 Height	5.906 In (15.000 cm)
Package 3 Width	5.906 In (15.000 cm)
Package 3 Length	15.748 In (40.000 cm)
Package 3 Weight	3.851 Lb(US) (1.747 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**