



Commercial status

End-of-Sale Notice : SEP 30, 2022

⚠ End-of-Sale Notice

Main

Range	Thorsman
Range of product	Thorsman Cintura
Product or component type	Cable tie
Colour tint	Clear
Quantity per set	Set of 100

Complementary

Maximum tightening diameter	102 Mm
Condition of use	Indoor
Mechanical robustness	Resistance to tearing: 54.5 daN
Material	PA (polyamide) 6.6 UV-stabilised
Length	368 Mm
Width	7.6 Mm
Net weight	0.005 Kg
Market segment	Small commercial

Environment

Fire resistance	650 °C / 30 s conforming to NF C 20-455
Flame retardance	Self-extinguishing conforming to UL 94 V2
Ambient air temperature for operation	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 Cm
Package 1 Width	1.6 Cm
Package 1 Length	23.5 Cm
Package 1 Weight	0.826 G

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	End of commerc. - Block
-----------------------	-------------------------