



Main

Range of product	Mureva FIX
Product or component type	Installation tie
Colour tint	Black
Quantity per set	100 pieces

Complementary

Minimum tightening diameter	8 Mm
Maximum tightening diameter	22 Mm
Mechanical robustness	Resistance to tearing: 36 daN Ø 20 mm
Material	PA (polyamide) 12 Rislan®
Length	132 Mm
Width	9 Mm
Net weight	0.002 Kg

Environment

Maximum humidity absorption	0.9 %
Ambient air temperature for operation	-60...85 °C 100 °C during 1000 hours 120 °C maximum
Flame retardance	HB conforming to UL 94
Standards	EN 50146
Environmental characteristic	UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.12 Cm
Package 1 Width	0.9 Cm
Package 1 Length	13.2 Cm
Package 1 Weight	2 G
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	8.5 Cm
Package 2 Width	10.5 Cm
Package 2 Length	15 Cm
Package 2 Weight	213 G
Unit Type of Package 3	CAR

Number of Units in Package 3	3000
Package 3 Height	35 Cm
Package 3 Width	34 Cm
Package 3 Length	42 Cm
Package 3 Weight	7.12 Kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**