

# Product data sheet

## Characteristics

# EPDU1232M

Easy PDU, Metered, Zero U, 22 kW, 230V, (18)  
C13 & (6) C19;IEC309



by Schneider Electric

Price\*: 1758.23 EUR



### Visão geral

Prazo de entrega	Normalmente em stock
------------------	----------------------

### Geral

Equipamento fornecido	Manual de instalação Kit de montagem sem ferramentas Suporte de montagem vertical
-----------------------	---

### Físico

Comprimento do cabo	1,98 M
Cor	Preto
Profundidade	4,44 Cm
Altura	150,6 Cm
Peso net	4,64 Kg
Largura	6,2 Cm

### Entrada

Limites da corrente de entrada	32 A
Load Capacity	22000 VA
Frequência da rede	50/60 Hz
Plug standard	IEC 60309 32 A 3P + N + PE
Tensão de entrada	Trifásico

### Saída

Number of power socket outlets	18 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	-------------------------------------

### Conformidades

Certificações do produto	CE EAC RCM TÜV
--------------------------	-------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative



## Ambiental

Temperatura do ar ambiente para a operação	-5...45 °C
Humidade relativa	5...95 %
Altitude de funcionamento	0...10000 ft
Temperatura ambiente para armazenamento	-25...65 °C
Humidade relativa de armazenamento	5...95 %
Altitude de armazenamento	0,00...15240,00 M

## Unidades de embalagem

Peso da embalagem (Lbs)	5,48 Kg
Pacote 1 Altura	1,66 M
Pacote 1 largura	160 Mm
Pacote 1 Comprimento	110 Mm

## Sustentabilidade da oferta

Diretiva RoHS da UE	Conforme  <a href="#">Declaração RoHS Da EU</a>
Sem mercúrio	Sim
Informações das isenções RoHS	 <a href="#">Sim</a>

## Garantia contractual

Garantia	1 ano para reparação ou substituição
----------	--------------------------------------

Product Life Status : **Comercializado**