



### Main

Range of product	Easy9
Product or component type	Residual current circuit breaker (RCCB)
Device short name	Easy9 RCCB
Poles description	4P
Neutral position	Left
[In] rated current	63 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Rated breaking and making capacity	630 A
Rated conditional short-circuit current	Easy9 MCB: 4500 A 63 A

### Complementary

Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	400 V AC 50 Hz
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	440 V AC
[Uimp] rated impulse withstand voltage	4 kV
Surge current	250 A
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Connection pitch	18 mm between phases
9 mm pitches	8
Height	82 mm
Width	72 mm
Depth	72 mm
Colour	Grey (RAL 7035)
Mechanical durability	5000 Cycles
Electrical durability	AC: 2000 cycles 400 V AC 50 Hz

Connections - terminals	Tunnel type terminal (top or bottom) 1...35 mm <sup>2</sup> rigid Tunnel type terminal (top or bottom) 1...25 mm <sup>2</sup> flexible
Tightening torque	3.5 N.M top or bottom
Market segment	Residential Small commercial

## Environment

Standards	IEC 61008-1
Product certifications	ISI[RETURN]CE
IP degree of protection	IP20
Pollution degree	2 conforming to IEC 61008-1
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 Cm
Package 1 Width	8 Cm
Package 1 Length	9 Cm
Package 1 Weight	354 G
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	9.2 Cm
Package 2 Width	9.7 Cm
Package 2 Length	25.5 Cm
Package 2 Weight	1.26 Kg
Unit Type of Package 3	S03
Number of Units in Package 3	27
Package 3 Height	30 Cm
Package 3 Width	30 Cm
Package 3 Length	40 Cm
Package 3 Weight	12.744 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts & cables product

Product Life Status : **Commercialised**