

## Galaxy VL 400 V UPS

### Classic Battery Cabinet Runtimes for 400 V

Battery runtimes are listed in minutes at 100% load. Battery runtimes are estimated values based on battery manufacturer data for operation at 25 °C.

Please note that not all battery solutions are available for all UPS ratings due to:

- The number of battery blocks in the specific battery solution differs from the specific UPS requirements.
- The specific battery solution would provide less than 5 minutes runtime with the specific UPS.
- The battery breaker rating in the specific battery solution does not match the specific UPS rating.

| UPS rating            | 200 kW   | 250 kW | 300 kW | 350 kW | 400 kW | 450 kW | 500 kW |
|-----------------------|----------|--------|--------|--------|--------|--------|--------|
| <b>Power factor</b>   | <b>1</b> |        |        |        |        |        |        |
| <b>2 x GVSCBC10A2</b> | 7.9      | 5.4    | –      | –      | –      | –      | –      |
| <b>2 x GVSCBC10B2</b> | 12.5     | 8.5    | 6      | –      | –      | –      | –      |
| <b>3 x GVSCBC10A2</b> | 14.0     | 10.0   | 7.9    | 6.1    | –      | –      | –      |
| <b>3 x GVSCBC10B2</b> | 22.5     | 16.5   | 12.5   | 9.7    | 7.6    | 5.9    | –      |
| <b>4 x GVSCBC10A2</b> | 21.0     | 15.0   | 12.0   | 9.7    | 8.0    | 6.5    | 5.4    |
| <b>4 x GVSCBC10B2</b> | 33.5     | 25.0   | 19.5   | 15.5   | 12.5   | 10.0   | 8.6    |