


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
HDA36150


 by **Schneider Electric**
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
For Use With: I-line Panelboards and Switchboards
Approvals: UL Listed - CSA Certified - IEC Rated
Mounting Type: I-Line Plug-On
Terminal Type: I-Line Connection (ON end) - Lugs (OFF end)
Wire Size: #14-3/0 AWG (Al/Cu)
Weight: 5 Pounds
Mounting Height: 4.5 Inches

Specification:

Description: PowerPact H-frame Thermal Magnetic Circuit Breaker
Number of Poles: 3-Pole
Ampere Rating: 150A
Voltage Rating: 600VAC
Interrupting Rating: 25kA at 240VAC - 18kA at 480VAC - 14kA at 600VAC
Fixed AC Magnetic Trip: Hold: 900A - Trip: 1700A
Phase Connection: ABC