


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**HMIGTO3510**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

UL Certifications:	UL/c-UL Listed, (UL508)
CSA Certifications:	CSA-C22.2 No.142-M1987
ANSI/ISA Certifications:	ANSI/ISA 12.12.01
CE Markings:	CE EN61000-6-2, EN61000-6-4, EN61131-2
WEEE 2002/96/EC:	Yes
RoHS 2002/95/EC:	Yes
RoHS China SJ/T 11363-2006:	Yes
Common Automation Protocols:	Modbus, Uni-TE, FIPWAY, FIPIO, Modbus Plus
Other Protocols:	PacDrive, Siemens, Omron, Mitsubishi, Rockwell
Operating Temperature Range:	0°C (32°F) to 50°C (122°F)
Storage Temperature Range:	-20 to 60 °C [-4 to 140 °F]
Relative Humidity"	0 to 90% non-condensing

**Specification:**

<b>Description:</b>	Human Machine Interface GTO3510
<b>Screen Type:</b>	TFT Color LCD (7.0 inch)
<b>Resolution:</b>	800 x 480 pixels (WVGA)
<b>Interface Ports:</b>	RS-232C, RS-485 RJ45
<b>Enclosure Rating:</b>	IP65, NEMA4x
<b>USB Ports:</b>	1 Type-A and 1 mini-B
<b>RAM:</b>	128kb SRAM with battery backup
<b>Storage:</b>	96MB App Flash
<b>Supply Voltage:</b>	24VDC ± 4.8