



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
HMIZRA1

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 NEMA Protection: Type 13 (outdoor), Type 4X (indoor)
 Storage Temperature: -20 to 60°C (-4 to 140°F)
 Operating Temperature: 0 to 50°C (32 to 122°F)
 IP Protection: IP65
 Humidity: 10% to 90% non-condensing
 Supply Voltage: Powered by USB
 Connection: USB 2.0
 Power: 2W

Specification:
 Description: USB Illuminated Switch
 Certifications: CE, C-Tick, GOST, UL/cUL listed
 Hazardous Locations: Class I Division 2 Groups A/B/C/D
 Buttons: 5, with tactile feedback
 Backlight: 6 programmable backlight colors per button
 Standards: CSA C22.2 No 142, EN 61000-6-2, EN 61000-6-4, ROHS 2002/95/EC, UL 508, EMC 2004/108/EC, ANSI/ISA 12-12-01, WEEE 2002/96/EC, CSA C22.2 No 213, RoHS China SJ/T 11363-2006