



Commercial status

End-of-Sale Notice : DEC 15, 2021

 End-of-Sale Notice

Main

Range of product	Harmony K
Accessory / separate part designation	M22 fixing nut
Accessory / separate part type	Nut
Accessory / separate part category	Mounting and fixing accessories
Accessory / separate part destination	For fixing operating head in an enclosure For fixing operating head on panel
Sale per indivisible quantity	5

Complementary

Net weight	0.007 Kg
------------	----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 Cm
Package 1 Width	3 Cm
Package 1 Length	8 Cm
Package 1 Weight	7 G

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	End of commerc. - Block
-----------------------	-------------------------