



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
LC1D09G7

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Rating: 600V / 9A
UL File/CCN: E164862 / NLDX
CSA File: LR43364 3211 04
Meets Standards: IEC 60647-4
Weight: 0.71 lb (0.32 kg)
Termination Method: Screw Clamp
Wire Size: Power: #10 - #18 AWG
 Control: #10 - #18 AWG
Terminal torque: Power: 15 lb-in (1.7 Nm)
 Control: 15 lb-in (1.7 Nm)
Mounting Hwd.: 35mm DIN Rail, #8 screw

Technical Information:

Specification:

Description TeSys D IEC Contactor - 9A - Vac Coil
Type TeSys D IEC Contactor - 9A - 120Vac Coil
Voltages Code: G7 at 120Vac 50/60 Hz

Coil Consumption: Inrush 70 VA
 Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
0.5 HP	1 HP	2 HP	2 HP	5 HP	7.5 HP