



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
LC1D150F7

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 Rating: 600V / 150A
 UL File/CCN: E164862 / NLDX
 CSA File: LR43364 3211 04
 Meets Standards: IEC 60647-4
 Weight: 2.5 lb (1.13 kg)
 Termination Method: Screw Clamp
 Wire Size: Power: #8 AWG - 250MCM
 Control: #14 - #18 AWG
 Terminal torque: Power: 100 lb-in (12 Nm)
 Control: 10 lb-in (1.2 Nm)
 Mounting Hwd.: 2 x 35mm DIN Rail, M6 screw

Specification:
 Description: TeSys D IEC Contactor - 150A - Vac Coil
 Type: TeSys D IEC Contactor - 150A - 110Vac Coil
 Voltages Code: F7 at 110Vac 50/60 Hz
 Coil Consumption: Inrush 280 - 350 VA
 Sealed 2 - 18 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
N/A	N/A	40 HP	50 HP	100 HP	125 HP