


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**LC1D32X7**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 32A  
 UL File/CCN: E164862 / NLDX  
 CSA File: LR43364 3211 04  
 Meets Standards: IEC 60647-4  
 Weight: 0.83 lb (0.375 kg)  
 Termination Method: Screw Clamp  
 Wire Size: Power: #6 - #14 AWG  
 Control: #10 - #18 AWG  
 Terminal torque: Power: 20 lb-in (2.5 Nm)  
 Control: 15 lb-in (1.7 Nm)  
 Mounting Hwd.: 35mm DIN Rail, #8 screw

**Specification:**

Description: TeSys D IEC Contactor - 32A - Vac Coil  
 Type: TeSys D IEC Contactor - 32A - 600Vac Coil  
 Voltages Code: X7 at 600Vac 50/60 Hz

Coil Consumption: Inrush 70 VA  
 Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
2 HP	5 HP	10 HP	10 HP	20 HP	30 HP